



Hanwei Group

Standalone Breathalyzer

www.hwsensor.com



AT319 Coin Operated Alcohol Tester

FEATURES

- Fuel cell sensor-accuracy and reliance
- Pre-calibrated sensor module-easy for maintenance
- AC110V/220V power supply
- Switchable result units(mg/l, g/l, %BAC, ‰BAC)
- Suitable for bar, restaurant, hotel, and night clubs, etc.
- Coin payment only


APPLICATION

Bar, hotel, restaurant, factory, workshop, office, hotel, mine, etc.



AT319, Coin operated Breath Alcohol Tester, is designed to measure alcohol concentration in the human body. With advanced fuel cell alcohol sensor, this device has excellent sensitivity and reproducibility. Reasonable and easy testing process, complete function makes it versatile in many occasions.

STRUCTURES



Pic 1

- | | |
|-----------------|-----------------|
| 1 Screw hole | 4 Straw exit |
| 2 Coin selector | 5 On/Off switch |
| 3 Lock | 6 Coin box |

Firstly please find a right place then fix the device on the wall (see Pic 1) by using the bolt packed along with the device. Or the tester can be put directly on the platform for use.

SPECIFICATIONS

Sensor Type	Fuel cell	Display	Four-digit digital tube
Detection Range	0.00 - 0.40%BAC, 0.00-4.00‰BAC 0.00 - 2.00mg/L; 0.00 - 4.00g/L	Power	AC110V-AC220V 50/60HZ
		Working Environment	0°C - 50°C, ≤95% RH, No dews
Accuracy	± 0.005 at 0.05%BAC	Working Time	Continuous
Pre-set Level	0.05%BAC; 0.50‰BAC; 0.25mg/L; 0.50g/L	Dimensions	310mm*141mm*450mm @4500g
Warm-up Time	<10 seconds	Installation	Wall-mounted
Testing Time	< 5 Sec	Payment term	Coins

Welcome to Hanwei !



汉威科技集团股份有限公司
Hanwei Electronics Group Corporation

ADD: No.169 Xuesong Road,National&HighTech Zone,
Zhengzhou 450001,Henan,China P.C: 450001

www.hwsensor.com
TEL: 86-371-67169070 / 80
FAX: 86-371-67169090
E-mail: sales@hwsensor.com