



Consumer Breathalyzer



AT8030 Fuel Cell Alcohol Tester


FEATURES

- Fuel cell sensor-accuracy and reliance
- Adjustable alarming threshold
- Testing records (maximum 10) review
- Switchable result units(mg/l, g/l, %BAC, ‰BAC)
- Anti-backflow mouthpiece for health and safety


APPLICATION

Car, hotel, home, workshop, office, etc.

STRUCTURES



- a. Mouthpiece
- b. Indicator light
- c. Display screen
- d. Press button
- e. Housing



- 1. Value display
- 2. Wait
- 3. Blow
- 4. Alarm
- 5. Battery
- 6. Test unit

SPECIFICATIONS

Sensor Type	Fuel cell	Display	AT8030:1.5inch LCD; AT8060: 1.6-inch LCD
Detection Range	0.00 - 0.40%BAC, 0.00-4.00‰BAC 0.00 - 2.00mg/L; 0.00 - 4.00g/L		Power
Accuracy	±0.01%BAC at 0.05%BAC	Working Environment	0°C - 50°C, ≤95% RH, No dews
Pre-set Level	0.05%BAC; 0.50‰BAC; 0.25mg/L; 0.50g/L	Working Time	>2000 blowing times (full charge)
Warm-up Time	<10 seconds	Dimensions	AT8030:127mm*53mm*22mm @75g AT8060: 122mm*67mm*31mm @120g
Testing Time	< 5 Sec		Testing Records

Welcome to Hanwei !



汉威科技集团股份有限公司
Hanwei Electronics Group Corporation

ADD: No.169 Xuesong Road,National&HighTech Zone,
Zhengzhou 450001, Henan, China P.C: 450001

www.hwsensor.com

TEL: 86-371-67169070 / 80

FAX: 86-371-67169090

E-mail: sales@hwsensor.com